

2.4/5 GHZ 7 DBI 6 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-7D-6RPSP-36

4

ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.485/5.15-5.85 GHz Gain: 7 dBi Polarization: 3 Vertical, 3 Horizontal Horizontal Beamwidth: $66^{\circ}/65^{\circ}$ Vertical Beamwidth: $66^{\circ}/62^{\circ}$ VSWR: $\leq 1.5:1$, max 2.0 Isolation: >30 dB Impedance: 50 Ω



MECHANICAL SPECIFICATIONS

Dimensions: 12.2" x 8.66" x 1.57" (310x220x40mm) Weight: 1.5 lb (0.68 kg) Installation: Flush Mount to Wall OR included Articulating Mount (included)



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 158°F (-40 to 70°C) Wind Velocity: 134 mph (216 km/h) IP Rating: IP66




Radome Material: ABS Connector: RPSMA Number of Leads: 6 Cable Length: 36" (910mm) Cable Type: RG402 Plenum

WARRANTY

2 Year Limited Warranty

3

HORIZONTAL



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2023 AccelTex Solutions. All Rights Reserved.

1.888.406.8906 SALES@ACCELTEX.COM

VERTICAL