



Titan (analogue), yellow, steel cord (0.455 metre), 18 button (CE Marked)

By Austdac
Catalog # 2000A2B21111A2A

Titan's aluminium body is robust and designed to last longer in hostile outdoor environments. Along with weather and vandal resistance, the Titan range meets the acoustic performance, reliability and varying applications demanded by today's markets. The standard analogue unit provides basic telephone functions and can be connected to any standard two-wire telephone line, including FXS ports, analogue PABX lines and PSTN.

Features

- Titan
- Stainless steel cord
- 18 Button full keypad
- CE Marked

General

CE Compliant	Yes
Catalog Number	2000A2B21111A2A
Color	Yellow
Connectivity Options	Analogue
Mount location	Surface-Mount & Post-Mounting
Operating Temperature	-20° C to +60° C
Output Level Ringer	80 dBA @ 2 ft.
Signal Type	Analog
Specifications	CE
Storage Temperature Range	-40°C to +70°C
Type	18 Button
Weather Rating	IP66

Dimensions



Dimensions	5.1 in x 8.07 in x 14.5 in
Dimensions - Shipping	15.5 x 8.75 x 5.5
Height	14.5 in
Length	5.1 in
Weight	11 lb
Width	8.07 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

CE Compliant	Yes
--------------	-----

Product Assets

[Certifications - Titan and Commander full dialling and auto-dialling analogue telephones Declaration of Conformity](#)
[Installation Manuals - Installation and User Guide for Titan Telephone \(1066\) Commander Telephone \(1065\) Standard keypad models](#)
[Literature - Titan - Metal Bodied Weather Resistant Telephone \(Analogue, Smart Analogue, VoIP\)](#)
[Specifications - 2000A2B21111A2A](#)



A Hubbell brand