



Titan (analogue), yellow, steel cord, 0 button (CB) - CE Marked

By Austdac
Catalog # 2000L2B3111K2E

Titan's aluminium body is robust and designed to last longer in hostile outdoor environments. Along with weather and vandal resistance, the Titan range meets the acoustic performance, reliability and varying applications demanded by today's markets. The standard analogue unit provides basic telephone functions and can be connected to any standard two-wire telephone line, including FXS ports, analogue PABX lines and PSTN.

General

CE Compliant	Yes
Catalog Number	2000L2B3111K2E
Color	Yellow
Connectivity Options	Analogue
Mount location	Surface-Mount & Post-Mounting
Operating Temperature	-20°C to +60 °C
Output Level Ringer	80 dBA @ 2 ft.
Signal Type	Analog
Specifications	CE
Storage Temperature Range	-40°C to +70°C
Type	0 Button
Weather Rating	IP66

Dimensions

Dimensions	5.1 in x 8.07 in x 14.5 in
Dimensions - Shipping	15.5 x 8.75 x 5.5
Height	14.5 in



Length	5.1 in
Weight	11 lb
Width	8.07 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

CE Compliant	Yes
--------------	-----

Product Assets

- [Certifications - Commander and Titan CB Declaration of Conformity](#)
- [Installation Manuals - Installation and User Guide for Titan CB \(1064\) Commander CB \(1064\) Weather Resistant Telephones](#)
- [Literature - Titan - Metal Bodied Weather Resistant Telephone \(Analogue, Smart Analogue, VoIP\)](#)
- [Specifications - 2000L2B3111K2E](#)



A Hubbell brand