

RPSMA JACK TO RPTNCP JACK ADAPTER



The AccelTex inline RF connector adapter converts an existing style or gender connector to easily mate with another style or gender. These adapters are built to minimize insertion loss and are an easy and efficient way to change styles and genders within an RF system.

Part Number: ATS-RPSMAJ-RPTNCJ

> ELECTRICAL SPECIFICATIONS

Impedance: 50Ω

Frequency Range: DC-5.85 GHz

VSWR: ≤1.3

Insertion Loss: ≤0.2dB

Center Conductor Contact Resistance: $\leq 10 m\Omega$ Outer Conductor Contact Resistance: $\leq 2.5 m\Omega$

Dielectric Withstand: 1000V RMS Insulation Resistance: $\geq 5000M\Omega$

> MECHANICAL SPECIFICATIONS

Connector 1 Style: RPSMA Jack Connector 2 Style: RPTNC Jack

Adapter Shape: Straight

Mating: 1/4-36UNS-2A and 7/16-28UNEF-2A

Durability: ≥ 500 Cycles

Body: Nickel Plated Brass

Insulator: Teflon

Contact Pin: Gold Plated Brass

> ENVIRONMENTAL SPECIFICATIONS

Operating Temperature: -67 to 311°F (-55 to 155°C)

> STANDARDS, TESTING AND CERTIFICATIONS

IEC 60169-15 and IEC 60169 –17 ROHS 2011/65/EU Compliant

> WARRANTY

1 Year Limited Warranty