



Speaker Amplifier Assemblies (VoIP)

By Austdac
Catalog # 10370-701

The VoIP Speaker Amplifier Assemblies enable broadcasting to personnel throughout a facility or area over an existing VoIP network via an external speaker(s) or connection to a central amplifier speaker system.

Features

- Wired
- One-way broadcasting from IP network
- Weatherproof enclosure
- Direct 120/240 VAC input power or PoE
- 30-watt speaker amplifier (into an 8-ohm speaker load)
- 10370-x01 series with 120/240 VAC input
- 24-watt, 70.7V or 100V audio output, 10370-x02 series with 120/240 VAC input
- 600-ohm audio output
- Two programmable dry contact closure outputs
- SIP compatible (RFC3261)
- Real-time alarm reporting via email, Syslog, or TMA software
- Configurable via web page, serial link or download
- Multicast capability, up to eight addresses

General

Catalog Number	10370-701
Color	Gray
Connectivity Options	VoIP
Output Level Speaker	8 Ohm
Signal Type	VoIP - SIP



Type	Speaker Amplifier Assemblies
Weather Rating	Rainproof (3R)

Dimensions

Dimensions	4.0 in x 9.25 in x 13.0 in
Height	13 in
Length	4 in
Weight	6.1 lb
Width	9.25 in

Electrical Ratings

Output Voltage	30 V
Signal	Ethernet
Voltage Rating Description	120/240 VAC/PoE

Certifications And Compliance

Certified Listed	FCC/IC
------------------	--------

Product Assets

- [Installation Manuals - Installation and Operation Manual - VoIP Interface/Amplifier Assemblies](#)
- [Literature - VoIP and WiFi Speaker Amplifier Assemblies](#)