



Indoor/Outdoor Compression Driver - 13314 Series (16 ohm)

By Austdac Pty Ltd
Catalog # [13314-002](#)

A compression drivers that is designed to provide optimum performance in both commercial and industrial applications. These indoor/outdoor compression drivers are commonly used in light and heavy manufacturing facilities with high ambient noise, and corrosive and hazardous environments.

Features

- Low Distortion, Superior Sound
- Rain-Tight, Chemical Resistant Housing
- Suitable for Harsh or Corrosive Environments
- Variable Impedance Drivers
- Fits GAI-TRONICS' Horns with 1 3/8" - 18 UNEF Threads
- NEMA 4X

General

Operating Temperature -40° C to +70° C (-40° F to +158° F)
UPC 850025795029

Dimensions

Weight 3.1 lb



Electrical Ratings

Impedance 16 ohm

Certifications and Compliance

Hazardous Rating(s)

- Class I, Div. 2, Groups A, B, C, D
- Class II, Div. 2, Groups F, G
- Class III, Div. 2

Nema Rating 4X

Product Assets

[Installation Manuals - Model 13314-002 Div. 2 Hazardous Area 16-Ohm Horn Driver](#)
[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
[Literature - Indoor / Outdoor Compression Driver](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
AUST-13314-002-SPEC-EN | REV 7/2023