



Corridor Surface-Mount VoIP Telephone (Auto-dial)

By Austdac
Catalog # 210-712



GAI-Tronics ADA-compliant corridor telephone with 29" handset cord, surface mount, signed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The telephones are programmed to automatically dial when the handset is taken off-hook (number/address programming via imbedded web browser). The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using power-over-Ethernet or an alternative power source.

Application

Corridor Installation, ADA compliant

General

| | |
|---------------------------|---------------------------------|
| Catalog Number | 210-712 |
| Color | Silver |
| Connectivity Options | VoIP |
| Mount location | Surface-Mount |
| Operating Temperature | -4°F to +131°F / -20°C to +55°C |
| Signal Type | VoIP - SIP |
| Specifications | UL/CSA, FCC |
| Storage Temperature Range | -40° C to +70° C |
| Temperature Rating | -4°F to +131°F (-20°C to +55°C) |
| Type | Auto-Dial |
| Weather Rating | Indoor |

Dimensions

| | |
|----------------|----------------------------|
| Cubic Capacity | 58.81095 cu.in |
| Depth | 3.27 in |
| Dimensions | 10.0 in x 5.5 in x 3.27 in |

| | |
|--------|---------|
| Height | 3.27 in |
| Length | 10 in |
| Weight | 5.5 lb |
| Width | 5.5 in |

Electrical Ratings

| | |
|----------------------------|--------------------|
| Signal | Ethernet |
| Voltage Rating | 24-48 VDC or PoE V |
| Voltage Rating Description | 24-48 VDC or PoE |

Certifications And Compliance

| | |
|------------------|--------------------|
| Certification | UL/CSA/FCC |
| Certified Listed | UL/CSA/FCC |
| Compliance | FCC CRF 47 Part 15 |
| Nema Rating | IP66 |

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide:](#)
- [Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)