



Indoor Rugged Telephone - Analog (Keypad)

By Austdac
Catalog # 246-001

This Indoor Analog Telephone is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) Hytrel® handset cord.



Features

- High-impact, Non-metallic Enclosure
- Extended Temperature Range: - 40°F to +140°F
- Braille Metallic Keypad
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-canceling Microphone and Hytrel® Coil Cord (6-ft extended)
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- FCC & IC Certified, UL60950 Listed

Application

Indoor Use

General

Catalog Number	246-001
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	92 dBA @ 2 ft.
Signal Type	Analog

Specifications
Type
Weather Rating

UL/CSA, FCC, IC
Keypad
Indoor

Dimensions

Dimensions	6.9 in x 8 in x 9.5 in
Height	9.5 in
Length	6.9 in
Weight	6 lb
Width	8 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Rugged Analog Telephones with Keypads](#)
- [Literature - Rugged Telephones - Keypad](#)