



Flush-panel Handset Telephone - Analog (Keypad)

By Austdac
Catalog # 276-001

The 27x series handset telephone is designed to flush or surface mount (using 236 series or 238 enclosure). This unit has a brushed stainless steel faceplate with a metallic non-moveable hookswitch. Standard equipment also includes a 29-inch lanyard armored cord and tamper resistant hardware.

Features

- Stainless Steel Construction
- Extended Temperature Range: - 40°F to +140°F
- Braille Metallic Keypad
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-cancelling Microphone and 29-inch Armored Cord
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- FCC & IC Certified, UL60950 Listed
- NEMA 3R Weatherproof Rated

Application

Indoor & Outdoor Use

General

Catalog Number	276-001
Color	Silver
Connectivity Options	Analog
Mount location	Flush-Mount
Output Level Ringer	86 dBA @ 2 ft.



Signal Type	Analog
Specifications	UL/CSA, FCC, IC
Type	Keypad
Weather Rating	Type 3R

Dimensions

Dimensions	2.51 in x 10.0 in x 12.0 in
Height	12 in
Length	2.51 in
Weight	6.5 lb
Width	10 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Rugged Analog Telephones with Keypads](#)
- [Literature - Rugged Telephones - Keypad](#)