



Outdoor Rugged Telephone - Analog/SMART (Keypad)

By Austdac
Catalog # 256-005



This outdoor series telephone includes a latching door and is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) Hytrel® handset cord. SMART models include the ability to be centrally monitored for health status via our TMA software.

Features

- High-impact, Non-metallic Enclosure
- Telephone Line Powered
- No External Power Needed
- Braille Metallic Keypad
- Handset with Noise-canceling Microphone and Hytrel® Coil Cord (6-ft extended)
- Hearing Aid Compatible Handset
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Surface-mount
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Conformal-coated PCBA
- Dual Output Control
- Three Number Rollover - Unit Dials Up to Three Different Numbers to Ensure Emergency Calls are Answered
- Email Notification of Unit Faults or Reports
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

Application

Outdoor Use

General

Catalog Number	256-005
Color	Gray
Connectivity Options	Analog/SMART
Mount location	Surface-Mount

Output Level Ringer	82 dBA @ 2 ft.
Signal Type	Analog
Specifications	UL/CSA, FCC, IC
Type	Keypad
Weather Rating	Type 3R

Dimensions

Dimensions	7.4 in x 9.4 in x 13.2 in
Height	13.2 in
Length	7.4 in
Weight	10 lb
Width	9.4 in

Electrical Ratings

Input Voltage	Phone Line
Signal	Phone Line

Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - SMART Handset Telephones with Keypads \(Model 226-005, 246-005, 256-005, and 276-005\)](#)
- [Installation Manuals - Telephone Management Application](#)
- [Installation Bulletin](#)
- [Installation Manuals - Telephone Management Application \(TMA\)](#)
- [User Guide](#)
- [Literature - SMART Rugged Telephones - Keypad](#)
- [Literature - Telephone Management Application \(TMA\)](#)