



Analog UL Class I Div 1 Telephone

By Austdac
Catalog # 352-001



GAI-Tronics introduces the world's first UL Class I Division 1 telephone and is available in standard analog. This rugged analog handset is UL approved to Class I Division 1 Groups B, C, & D, Class II Groups F & G and Class III, Type 4X, and ABS Type Approved. Analog variants are available with relay contact. Ring relay contacts are 5A, 250 V ac / 30 V dc rated.

General

Catalog Number	352-001
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	External required
Signal Type	Analog
Specifications	UL/cUL, ABS, FCC
Weather Rating	Type 4X

Dimensions

Cubic Capacity	1175.265 cu.in
Depth	9.36
Height	12.25 in
Weight	28 lb
Width	10.25 in

Electrical Ratings

Input Voltage	Phone Line
---------------	------------

Signal

Phone Line

Certifications And Compliance

Certification	<ul style="list-style-type: none"> • UL • cUL
Compliance	Telecoms Compliance to Standards: FCC CFR 47 Part 15
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Division 1, Groups B, C, & D • Class II, Division 1, Groups F & G • Class III, Division 1

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Division 1 Telephones \(Model 352-001, 352-002, 352-003, and 352-004\)](#)
- [Literature - UL Class I Division 1 Telephones \(VoIP / SMART / Analog\)](#)