



# RED ALERT® VoIP Hands-free Emergency Telephones - Model 393-710

By Austdac  
Catalog # 393-710



GAI-TRONICS' RED ALERT® Hands-free VoIP Surface-mount Telephones are designed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet and operate using power-over-Ethernet or an alternative power source. The VoIP telephone features real-time alarm reporting that enables system supervisors to monitor the phone's activity and address callers needs or maintenance issues immediately.

## Application

Emergency Telephone Communications (campuses, parking lots, paths)

## General

Catalog Number	393-710
Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> <li>• Emergency Telephones</li> <li>• HELP Button</li> </ul>
Weather Rating	Type 3R

## Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Height	9.5 in
Length	4 in
Weight	4 lb
Width	8 in

## Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

## Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

## Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide:](#)
- [Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Literature - VoIP Hands-free Telephones - Surface-mount](#)