



NEMA 4X VoIP Rugged Handset Telephone, Keypad, Armored Cord, Red

By Austdac
Catalog # 354-710RDAC



GAI-TRONICS' VoIP NEMA 4X Rugged Handset Keypad Telephones are designed to provide direct, point-to-point communications between personnel via an existing Internet Protocol LAN. These telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using Power-over-Ethernet (PoE) or an alternative, external power source. This VoIP Handset Telephone offers standard telephone functionality with active dial tone when the handset is removed from its cradle. This rugged telephone is weatherproof rated as NEMA 4X and will withstand a direct spray wash-down or severe weather conditions. The engineered plastic enclosure, conformal-coated printed circuit board, keypad protective boot, and stainless steel panel and hardware provide the maximum resistance to corrosion.

Application

Outdoor & Indoor Use (NEMA 4X)

General

Catalog Number	354-710RDAC
Color	Red
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> • Cord Type: 15-in. Armored Cord • Keypad
Weather Rating	Type 4X

Dimensions

Cubic Capacity	1201.725 cu.in
----------------	----------------

Depth	10.5 in
Dimensions	14.6 in x 10.9 in x 10.5 in
Height	10.5 in
Length	14.6 in
Weight	15 lb
Width	10.9 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15
Nema Rating	4X

Product Assets

[Configuration Guide - VoIP Telephone Basic Configuration Guide Literature - NEMA 4X VoIP Handset Telephone \(Keypad\), Model 354-710 Series](#)