



HUBBCOM™ IP Devices with Temperature Sensing (Desktop, Wall-mount, Handset)

By Austdac
Catalog # [GSC1100TS](#)



The HUBBCOM™ IP device has a multi-functional design, providing solutions for all your control and communication needs. It provides the ability to combine web application control, VoIP SIP telephone operation, speaker broadcasts, and point-to-point serverless IP communication (audio and/or video). HUBBCOM™ TS devices add another critical function for security applications. This model adds a temperature sensor to the access control feature. After scanning their card, the user simply aligns themselves with the template on the screen and the station will read their temperature. Access will be granted if their temperature is within a programmable range.

Features

- Card Access control with built-in pre-entry temperature check
- Point-to-Point, Serverless Audio & Video
- Paging with Intercom (Soft Zoning, Multiple Conference Calls, Serverless)
- SIP Telephone
- Web Portal Access (applications)
- 7-inch Capacitive Touchscreen
- ONVIF-Compatible HD Camera
- Desktop / Handset
- Intuitive Operation
- 24 V dc or PoE / PoE+ Input
- Integral 2 W Speaker
- 8 Ohm, 8 W Speaker Output
- Two (2) Isolated Volt-free Outputs
- WiFi (802.11 a/b/g/n + MIMO)
- Bluetooth (Version 4.1 + CSA2 support / BLE)

General

Catalog Number	GSC1100TS
Operating Temperature	0° C to 50° C

Power	PoE / PoE+, 802.3af compliant (via RJ45)
UPC	850025795395

Dimensions

Weight	3 lb
--------	------

Certifications And Compliance

Compliance	FCC CRF 47 Part 15
------------	--------------------

Product Assets

- [Brochures - HUBBCOM™ Solutions Brochure - Communications & Control](#)
- [Brochures - HUBBCOM™ Solutions Brochure - Communications & Control](#)
- [Installation Manuals - HUBBCOM™ Dual-Port Desktop/Wall-mount Smart Controllers](#)
- [Installation Manuals - ADDENDUM-HUBBCOM™ Temperature Sensor Configuration and Operation](#)
- [Literature - HUBBCOM™ IP Devices with Temperature Sensing](#)
- [Video - HUBBCOM™ Temperature Sensing](#)