



RED ALERT® WiFi VoIP Hands-free Telephones - Model 393AL-810A

By Austdac
Catalog # 393AL-810A

These WiFi VoIP Surface-Mount Telephones are designed to provide direct point-to-point communications between personnel over an existing wireless local area network (WLAN), meeting IEEE 802.11 b/g standards. These telephones will operate from an external dc power source which is the only wiring required for operation.



Application

Emergency Telephone Communications (campuses, parking lots, paths)

General

Catalog Number	393AL-810A
Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> • Emergency Telephones • Keypad • HELP Button & CALL Button
Weather Rating	Type 3R

Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Height	9.5 in
Length	4 in
Weight	8.5 lb
Width	8 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide:](#)
- [Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Literature - WiFi VoIP Hands-free Telephones - Surface-mount](#)