

RED ALERT® VoIP Flush-Mount Telephones - Model 398-711

By Austdac
Catalog # 398-711



GAI-TRONICS' RED ALERT® Hands-free VoIP Flush-Mount Telephones are designed to provide direct point-to-point communications between personnel throughout a facility over an existing internet protocol LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet and operate using power-over-Ethernet or an alternative power source. The VoIP telephone features real-time alarm reporting that enables system supervisors to monitor the phone's activity and address callers needs or maintenance issues immediately.

Features

- Power Over Ethernet or Alternative 24-48 V dc Supply
- SIP Compatible
- Four Inputs and Two Outputs Per Phone
- Auto Answer
- Multicast Capable (Up to 8 Addresses)

Application

Emergency Telephone Communications (campuses, parking lots, paths)

General

Catalog Number	398-711
Color	Silver
Connectivity Options	VoIP
Mount location	Flush-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> • Keypad • CALL Button
Weather Rating	Type 3R

Dimensions

Dimensions	2.38 in x 10.0 in x 12.0 in
Height	12 in
Length	2.38 in
Weight	7.2 lb
Width	10 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide:](#)
- [Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Literature - VoIP Hands-free Telephones - Flush-mount](#)
- [Specifications - 398-711](#)