



RED ALERT® VoIP Flush-Mount Telephones - Model 398-711

By Austdac
Catalog # 398-711



GAI-TRONICS' RED ALERT® Hands-free VoIP Flush-Mount Telephones are designed to provide direct point-to-point communications between personnel throughout a facility over an existing internet protocol LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet and operate using power-over-Ethernet or an alternative power source. The VoIP telephone features real-time alarm reporting that enables system supervisors to monitor the phone's activity and address callers needs or maintenance issues immediately.

Application

Emergency Telephone Communications (campuses, parking lots, paths)

General

Catalog Number	398-711
Color	Silver
Connectivity Options	VoIP
Mount location	Flush-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> • Keypad • CALL Button
Weather Rating	Type 3R

Dimensions

Dimensions	2.38 in x 10.0 in x 12.0 in
Height	12 in
Length	2.38 in
Weight	7.2 lb
Width	10 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Literature - VoIP Hands-free Telephones - Flush-mount](#)