



ARRAN H/O

Industrial LED Floodlight

The industrial **Arran High Output** is a powerful LED floodlight delivering a uniform photometric distribution, whilst providing a comparable output to traditional high wattage HID floodlights.

An impressive performance of 90,000 maintenance free hours at 25°C, coupled with an extensive temperature range from -50°C up to +55°C makes the Arran H/O a truly global lighting solution.

The great versatility of this luminaire allows a variety of mounting options covering a wide range of Industrial installations.



ERC CE

International Approvals

Mounting Options

Floodlight. Pole/Column. Pendant. High Bay.

Standard Specification

Arran High Output LED Floodlight

Enclosure	Aluminium alloy (1050A H14) with RAL 7040 epoxy powder finish
Entry	2 x 20mm clearance holes
Termination	3 core 6mm ² max. conductor with looping
Installation	Stirrup mounting bracket
Control Gear	Electronic Driver
Colour Temperature (CCT)	5000K (Cool White)
Colour Rendering Index (Ra)	>70
Maintenance	M5 Slotted Screws
Ingress Protection	IP66
Surge Protection	4kV line to line, 6kV line to earth
Electrical Supply	120-277V AC 50/60Hz 140-273V DC

Features

- ◆ Highly **Energy Efficient**
- ◆ **Instant on** crisp white light output
- ◆ **Lower power consumption** than HID lamps
- ◆ **Lower temperature applications** to -50°C
- ◆ **90,000 maintenance free hours** at 25°C

Std. Cat No.	Delivered Output	Power Consumption	Ambient °C	Weight
ARHI/31L/LE	34420 lm	255W	-50 to +40	14kg
ARHI/40L/LE	45963 lm	389W	-50 to +40	14kg

Options - Suffix to Catalogue No.			
/25	25mm cable entries	/SRG	Surge Protection (20kA and 10kV)
/HT	High Temperature to +55°C (40L output reduces by 10% at +55°C to prolong LED and Driver life)		

Accessories *Accessories should be ordered separately*

	Order Code
Wire Guard (2 required per floodlight)	SARR1-0001
Anti Glare Shield	SAH04-0001
Pole Mounting Bracket Assembly	S2400-0002

