



# RED ALERT® VoIP Emergency Telephones - Model 397-710

By Austdac Pty Ltd  
Catalog # 397-710



GAI-TRONICS' RED ALERT® Hands-free VoIP Flush-Mount Telephones are designed to provide direct point-to-point communications between personnel throughout a facility over an existing internet protocol LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet and operate using power-over-Ethernet or an alternative power source. The VoIP telephone features real-time alarm reporting that enables system supervisors to monitor the phone's activity and address callers needs or maintenance issues immediately.

## Application

Emergency Telephone Communications (campuses, parking lots, paths)

## General

Color	Silver
Connectivity Options	VoIP
Construction	Front Panel: 14-Gauge Type 304 Brushed Stainless Steel; Dust Cover: 16-Gauge Cold-Rolled Steel With Black Polyurethane Finish
Mount location	Flush-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"><li>Emergency Telephones</li><li>HELP Button</li></ul>
Weather Rating	Type 3R

## Dimensions

Dimensions	2.38 in x 10.0 in x 12.0 in
Height	12.0 in
Length	2.38 in
Weight	7.2 lb
Width	10.0 in

## Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

## Certifications and Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

## Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Installation Manuals - RED ALERT® Hands-free VoIP Telephone Manual](#)
- [Literature - VoIP Hands-free Telephones - Flush-mount](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
AUST\_397-710\_SPEC | REV 3/2023