



## B483611CH

by Wiegmann  
Catalog ID: B483611CH

N12 JIC Continuous Hinge 48X36X11 Carbon Steel - Gray

- Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Doors are sealed with poured-in-place polyurethane gasket. External screw clamps on door. Continuously hinged door is removable by pulling hinged pin. Print pocket is provided. Door and body stiffeners are provided for added rigidity. Collar studs are provided for mounting optional back panels. External mounting feet. Ground stud located in door.

## Product Details

### General

|               |  |
|---------------|--|
| Application   | Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door provides convenient access. Designed to provide protection from dust, dirt, oil, and water. |
| Color         | Gray   |
| Construction  | Continuously Welded Seams  |
| Cover Type    | Hinged Cover   |
| Finish Type   | Textured   |
| Latches Type  | Clamps   |
| Listings      | UL, CSA  |
| Material      | Carbon Steel   |
| Mounting Type | Wall Mount   |
| Type          | Enclosure  |
| UPC           | 786725335824   |

### Dimensions

|        |        |
|--------|--------|
| Depth  | 11 in  |
| Height | 48 in  |
| Weight | 129 lb |
| Width  | 36 in  |

### Certifications and Compliance

|                  |  |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul> |
| Nema Rating      | NEMA 12  |
| UL Listed        | Yes  |