



## Weatherproof Lampholder, 75-150W Par 38 Lamps, White

By Bell  
Catalog # 5606-1



Weatherproof Lampholder, 75-150W Par 38 Lamps, White.

### Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Extra long wire leads for easy hook-up
- Porcelain socket
- Inside Gasket
- Multi-lingual instructions in each package
- 1/2 in. locknut
- Rugged die cast construction
- State of the art powder coat finish provides maximum weatherability and scratch resistance
- Extra-long wire leads and 1/2 lock nut for easy hook up
- Porcelain sockets
- Locking swivel knuckle

### General

Adjustable Detection Sensitivity	No
Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Construction	Metallic
Dusk to Dawn	No
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"><li>• Incandescent</li><li>• PAR 38</li></ul>
Material	Die Cast Aluminum
Type	<ul style="list-style-type: none"><li>• Lighting</li><li>• Lighting</li></ul>
UPC	050169560617
Weather Resistant	Yes

### Dimensions

Detection Range (ft.)	75 ft
Dimensions	5 in x 2.094 in x 2.094 in
Height	2.094 in
Length	5 in
Range of Motion	110 °
Weight	0.34 lb
Width	2.094 in

### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
ENERGY STAR Certified	No
Industry Standard(s)	UL 1598

### Logistics

Carton Quantity	30
Packaging Type	Shrink
Pallet Quantity	4500
Standard Package	30

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Sales Drawings - 5606 series, 5612-0](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BELL\_CA-5606-1-SPEC-EN | REV 1/2024

