



BELL Black Screw-in Replacement Light Sensor

By Bell
Catalog # PE100

BELL Black Screw-in Replacement Light Sensor



Features

- Durable Weatherproof construction.
- Built in time delay prevents operation triggered by auto headlamps or other temporary light flashes.
- Rated 1000 Watt
- Durable weatherproof construction
- Dusk to dawn operation
- Fits 1/2 in. outlet opening
- Black color

General

Catalog Number	PE100
Color	Black
EU RoHS Indicator	No
Fixture Type	Architectural; Flood
Material	Plastic
Type	Photocell
UPC	092326111850
Weather Resistant	Yes

Dimensions

Depth	1.65
Height	2.06 in

Weight	0.108 lb
Width	1.13 in

Electrical Ratings

Voltage Rating	120 V
----------------	-------

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Carton Quantity	10
Packaging Type	Polybag
Pallet Quantity	7200
Standard Package	20

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Sales Drawings - PE100](#)
- [Sales Drawings - PE 100 Wiring Instruction](#)
- [SDS - HCC SDS](#)
- [Specifications - PE100](#)
- [Terms and Conditions - HCC Terms & Conditions](#)