



\* Representative image

# Righthand Opening, 14.4kV, 110kV LIW, 600A Fused By-Pass Switch with 200 Amp Type C Fuse Tube.

by CHANCE Utility  
Catalog ID: BPFRI2P

Righthand Opening, 14.4kV, 110kV LIW, 600A Fused By-Pass Switch with 200 Amp Type C Fuse Tube.

- Must use removable buttonhead fuse links.

## Product Details

### General

Blade Type	Solid Copper (two blade truss-member)
Color - Insulator	Sky Gray
Contact	Silver
Description - Replacement Fuse Holder	T710-143T
Insulator Type	N/A
Material - Base	Galvanized Steel per ASTM A153
UPC	096359452126

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	15.5" (393.7mm)
Current Overload - 8hr Emergency	1080 A (switch circuit)
Interrupt Rating	12,000 A
Reference Voltage Limit - Minimum	14.4kV
Temperature Rise - Max.	27.5° C (Fuse Circuit)
Temperature Rise - Max. at 600A	25.7° C (switch circuit)
Voltage - Maximum	15 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical (switch circuit)
Withstand Current - Short Time (10 cycles)	65kA peak (switch circuit)

### Certifications and Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

### Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

**Domestic Customer Service**  
 Hubbell Power Systems  
 210 N. Allen Centralia, MO 65240 USA  
 Phone: (573) 682-5521  
 Fax: (573) 682-8475  
 Email: hpscsc@hubbell.com

**International Customer Service**  
 Phone: +1-573-682-5521  
 Fax: +1-573-682-8516  
 Email: hpsintlcs@hubbell.com

