



\* Representative image

# Lefthand Opening, 25kV, 150kV LIW, 600A Fused By-Pass Switch with 100 Amp Type C Fuse Tube.

by CHANCE Utility  
Catalog ID: BPFL21

Lefthand Opening, 25kV, 150kV LIW, 600A Fused By-Pass Switch with 100 Amp Type C Fuse Tube.

## Product Details

### General

Blade Type	Solid Copper (two blade truss-member)
Color - Insulator	Sky Gray
Contact	Silver
Description - Replacement Fuse Holder	T710-311T
Insulator Type	N/A
Material - Base	Galvanized Steel per ASTM A153
UPC	096359387855

### Dimensions

Weight	206.78 lb
--------	-----------

### Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	24" (609.6mm)
Current Overload - 8hr Emergency	1080 A (switch circuit)
Interrupt Rating	8,000 A
Reference Voltage Limit - Minimum	25kV
Temperature Rise - Max.	16.1° C (Fuse Circuit)
Temperature Rise - Max. at 600A	25.7° C (switch circuit)
Voltage - Maximum	27 kV
Withstand Current - Short Time (1 sec)	25kA, symmetrical (switch circuit)
Withstand Current - Short Time (10 cycles)	65kA peak (switch circuit)

### Certifications and Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

### Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)