



# ACC-ECTA1214, Vertical 90 Degree Edge Clip with Nylon12 Cable Tie, 14"

By Burndy  
Catalog # [ACC-ECTA1214](#)

Wiley Edge Clip with Cable Tie, Vertical (90 deg.) parallel installation



## Features

- Route cable bundles without the need for mounting holes or additional hardware
- Installs in a vertical/parallel (90°) or horizontal/perpendicular (180°) orientation
- Steel lances securely anchor clips to module frames or purlins
- Offered in various nylon types with 50 lb tensile strength: UV resistant, high impact heat stabilized Nylon 6/6
  - UV resistant Nylon 12 which provides excellent UV, chemical and moisture resistance

## Application

- For routing cable bundles without requiring mounting holes or additional hardware, Available in Nylon 6/6 or Nylon 12 for either horizontal/perpendicular (90°) or vertical/parallel (180°) styles
- 50 lb tensile strength, Steel lances securely anchor clips to module frames / purlins, 3 standard cable tie lengths (8", 11", 14") encompass maximum bundle diameters of 1.95" to 3.94"
- Custom lengths available

## General

Catalog Number	ACC-ECTA1214
Installation Type	Vertical (90 deg.) parallel installation
Material	Nylon 12
Tensile Strength	50 lb.
UPC	621945554368

## Dimensions

Dimension - Bundle Diameter	3.94 in
Max inch	
Length	17 in

## Certifications And Compliance

Certification - CSA Approved	N
Certification - cULus	N
Certified Listed	UL62275 Recognized
Industry Standard(s)	UL62275 Recognized

## Logistics

Carton Quantity	1000
-----------------	------

## Product Assets

[Catalogs - Wiley\\_WireManagementSolutions\\_Cat](#)  
[Catalogs - Section E4 - Wiley Grounding](#)  
[Catalogs - Section G - Wire Management](#)  
[Certifications - UL Certificate of Compliance UL 62275](#)  
[Sales Drawings - 50100741](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-ACC-ECTA1214-SPEC-EN | REV 6/2024