



AT22A20A30, Angled V Substation Connector

By Burndy
Catalog # [AT22A20A30](#)



Substation Connectors.

Application

Substation

General

Connector Type	A-Frame
Installation Torque	480 lb-in
Recommended Run in-lb	
Installation Torque	480 lb-in
Recommended Tap in-lb	
Material	Aluminum Alloy, Cast
Material - Hardware	Aluminum Alloy
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	30 Degree
Plated	N
Plating Type	Unplated
UPC	781810286791
UPC 12 Digit	7818102867911

Dimensions

Connector Angle	30 Degree
Dimension - B Length inch	6.00 in
Dimension - Height inch	13.12 in
Dimension - L Length Overall mm	315 mm
Dimension - Length BB inch	5.00 in
Dimension - Length Overall inch	12.42 in

Conductor Related

Conductor - AL Tube Std Run	4 IPS
Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Tap	3 IPS
Conductor - AL Tube Std Tap Range	3 IPS

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[3D Models - AT22A20A30_MODEL-PDF](#)
[3D Models - AT22A20A30_MODEL-STEP](#)
[3D Models - AT22A20A30_MODEL-IGES](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sc208096](#)



A proud member of the Hubbell Family.