



AT24A19A30SS, Angled V Substation Connector

By Burndy
Catalog # [AT24A19A30SS](#)



Substation Connectors.

Application

Substation

General

Connector Type	A-Frame
Installation Torque	660 lb-in
Recommended Run in-lb	
Installation Torque	660 lb-in
Recommended Tap in-lb	
Material	Aluminum Alloy, Cast
Material - Hardware	Stainless Steel
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	30 Degree
Plated	N
Plating Type	Unplated
UPC	621945336773
UPC 12 Digit	6219453367733

Dimensions

Connector Angle	30 Degree
Dimension - B Length inch	6.00 in
Dimension - Height inch	12.15 in
Dimension - L Length Overall mm	338 mm
Dimension - Length BB inch	4.50 in
Dimension - Length Overall inch	13.32 in

Conductor Related

Conductor - AL Tube Std Run	5 IPS
Conductor - AL Tube Std Run Range	5 IPS
Conductor - AL Tube Std Tap	2 1/2 IPS
Conductor - AL Tube Std Tap Range	2 1/2 IPS

Certifications and Compliance

Standards - RoHS Compliance UI Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Sales Drawings - sc208096](#)



A proud member of the Hubbell Family.