



AYP4, Compression Pin Adapter, 4 AWG, .23" Pin Dia, AL9CU

By Burndy
Catalog # [AYP4](#)

Aluminum Compression Adaptor, 4 AWG, 0.23" Plug Diameter, 0.68" Plug Length, Al/Cu Rated, Tin Plated.



Features

- All-aluminum electro-tin plated design eliminates possible bi-metallic corrosion
- Provides the shortest connector length design possible permitting easy installation in equipment with limited working space
- Solid electro-tin plated aluminum plug
- Proper electrical connection made easily and eliminates the "how tight is tight" issue
- Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to connect equipment
- Offset plug design available in sizes 2/0 through 750 kcmil providing flexibility and maximizing the use of limited space while eliminating interference between conductors and equipment
- Electro-tin plating resists corrosion
- Factory pre-filled with PENETROX oxide inhibiting compound with conductive metallic particles to penetrate aluminum oxide between strands and forms an air-tight connection
- EPDM rubber covers supplied with each connector and rated for 600V eliminating taping
- Only 5 die sets are required to install the complete line from #6 to 750 kcmil reducing inventory requirements
- Supplied in plastic convenience pack so cover and connector are kept together and free of foreign material until opened
- Connectors are clearly marked with catalog number, wire size, along with a color-coded die index providing clear, easy to use information

Application

- Wire Termination

General

Color Code	Tan
Connector Type	INLINE PIN
Die Index	296
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Insulation	Y
Insulation Type	EPDM Rubber
Material	ALUMINUM
Physical Attribute - Number of	1

Dimensions

Dimension - A Outside Diameter inch	0.60 in
Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - B Outside Diameter inch	0.23 in
Dimension - L Length Overall mm	47 mm
Dimension - Length Overall inch	1.85 in
Dimension - P inch	0.68 in
Dimension - Strip Length inch	1-1/16
Equivalent Pin Size	4 AWG

Electrical Ratings

Voltage - Maximum Voltage Rating	35000 V
	35 kV

Conductor Related

Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor - Copper DLO Size	6 AWG
Conductor - Copper DLO Size Range	6 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Str Compact Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	ALUMINUM / COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Crimps Required		Certification - UL Recognized	No
Pin Type	Solid	Certification - cULus	No
Plated	Y	Industry Standard(s)	UL 486A-486B
Plating Type	Tin	Standards - Industry Standards Met	UL 486A-486B
Sub Brand	HYPLUG	Standards - RoHS Compliance Status	CM
Temperature Rating	194	UL Listed	Yes
Terminal Type	Pin		
Trade Name	HYPLUG™		
Type	<ul style="list-style-type: none"> • Aluminum Pin Adapters • Aluminum Pin Adapters 		
UPC	781810737521		
UPC 12 Digit	7818107375211		

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	11600

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50103891](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-AYP4-SPEC-EN | REV 5/2024