



AGSKIT2, Splice Kit, 8-2 AWG, Heavy Wall Heat Shrink Sleeve, Al/Cu Rated

By Burndy
Catalog # [AGSKIT2](#)



Splice Kit, 8-2 AWG, w/ Heavy Wall Heat Shrink Sleeve, Al/Cu Rated.

Application

For All Aluminum or Copper/Aluminum Combinations

General

Connector Type	Splice/Heat Shrink Kit
EU RoHS Indicator	Yes
Hex Size	Slot
Insulation	Y
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SPLICE KIT
Temperature Rating	194° F
Type	AGSKIT, Above Grade
UPC	781810175293
UPC 12 Digit	7818101752933

Dimensions

Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Size Range	8 AWG-2 AWG
Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor Size	8-2 AWG
Conductor Type	<ul style="list-style-type: none">AL C Str-SizeCU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SD..211383-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-AGSKIT2-SPEC-EN | REV 8/2023

