



Aluminum Mechanical Splice, 4/0-6 AWG, 9/16" Screw Dia, 2 Screws, 5/16" Hex Size, Al/Cu Rated, Tin Plated

By Burndy
Catalog # [AMS4/0](#)



Aluminum Mechanical Splice, 4/0-6 AWG, 9/16" Screw Dia, 2 Screws, 5/16" Hex Size, Al/Cu Rated, Tin Plated.

Features

- Standard mounting hole diameter is .562" for 1/2" bolts
- The end wall within the cable socket of this design is solid and pressure tight
- Connectors are pre-filled and plugged with electrical joint compound
- Marked with catalog number, conductor size and die reference
- Meets performance requirements of ANSI C119.4

Application

For Use With Copper And Aluminum Conductors

General

Catalog Number	AMS4/0
Connector Type	In-Line
Die Size	<ul style="list-style-type: none"> • EEI 11A • Burndy WK840 • Burndy 249 • Kearney 840 • T&B TX • T&B 76
EU RoHS Indicator	Yes
Hex Size	5/16
Installation Torque Recommended in-lb	275 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Sub Brand	SPLICER/REDUCER
Temperature Rating Type	194° F
Temperature Rating	AMS, Dual Rated
UPC	781810241028
UPC 12 Digit	7818102410288

Dimensions

Depth	0.56 in
Dimension - H1 Height inch	1.09 in

Conductor Related

Conductor - ACSR Cmpnt Size	250 kcmil-300 kcmil
Conductor - ACSR Str Size	4/0 AWG & 250 kcmil
Conductor - AL Str Run	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	6 AWG-4/0 AWG
Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	6 AWG-4/0 AWG
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	6 AWG-4/0 AWG
Conductor - Copper Solid Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Run Range	6 AWG-4/0 AWG
Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-4/0 AWG
Conductor - Copper Str Compact Size	250 kcmil-300 kcmil
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	6 AWG-4/0 AWG
Conductor - Copper Str Size	4/0 AWG & 250 kcmil
Conductor - Copper Str Size Range	6 AWG-4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	6 AWG-4/0 AWG

Dimension - Height fraction	1-3/32
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.31 in
Dimension - Width fraction	1 in
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm
Length	3.25 in
Width	0.91 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Size 6-4/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	ANSI C119.4
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	240
Minimum Pack Quantity	1

Product Assets

- [3D Models - AMS40_MODEL-STEP](#)
- [3D Models - AMS40_MODEL-PDF](#)
- [3D Models - AMS40_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_AMS_Lineart](#)
- [Sales Drawings - sd207208-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-AMS40-SPEC-EN | REV 6/2024