



AT22A19A30, Angled V Substation Connector

By Burndy
Catalog # [AT22A19A30](#)



Substation Connectors.

Application

Substation

General

Connector Type	A-Frame
Installation Torque	480 lb-in
Recommended Run in-lb	
Installation Torque	480 lb-in
Recommended Tap in-lb	
Material	Aluminum Alloy, Cast
Material - Hardware	Aluminum Alloy
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	30 Degree
Plated	N
Plating Type	Unplated
UPC	781810159101
UPC 12 Digit	7818101591011

Dimensions

Connector Angle	30 Degree
Dimension - B Length inch	6.00 in
Dimension - Height inch	11.23 in
Dimension - L Length Overall mm	301 mm
Dimension - Length BB inch	4.50 in
Dimension - Length Overall inch	11.87 in

Conductor Related

Conductor - AL Tube Std Run	4 IPS
Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Tap	2 1/2 IPS
Conductor - AL Tube Std Tap Range	2 1/2 IPS

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sc208096](#)



A proud member of the Hubbell Family.