



# BA14E14, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # [BA14E14](#)



Vinyl Ring Terminal For 16 - 14 AWG.

## Application

- For Commercial, Light Duty Industrial Control and Power Circuit Applications

## General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electroplated
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	<ul style="list-style-type: none"><li>Ring Tongue</li><li>Ring Tongue</li></ul>
UPC	781810026632

## Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	10/37 in
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	0.99 in
Dimension - Pad Width inch	0.40 in
Dimension - Stud Size inch	1/4 in
Dimension - Z (inch)	0.36 in

## Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG; 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_BA16E6\\_LineArt](#)  
[Sales Drawings - 50093722](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BA14E14-SPEC-EN | REV 5/2024