

# BD18TN 18 inch Flexible Copper Braid

By Burndy  
Catalog # [BD18TN](#)



Flexible Tin Copper Braid 18 inches long.

## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

Catalog Number	BD18TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	781810421178
UPC 12 Digit	7818104211788

## Dimensions

Dimension - L Length Overall	457 mm
mm	

Dimension - Length Overall	18.00 in
inch	
Length	18 in

## Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - BD18TN\\_MODEL-PDF](#)
- [3D Models - BD18TN\\_MODEL-STEP](#)
- [3D Models - BD18TN\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BD\\_Lineart](#)
- [Sales Drawings - 10044985](#)
- [Specifications - BD18TN](#)