



# BA14EL8M, Vinyl Locking Fork Terminal For 16 - 14 AWG (Tape Mounted)

By Burndy  
Catalog # [BA14EL8M](#)

Fork Tongue Terminal, 16-14 AWG, #8 Stud, Polyvinylchloride Insulated, Tin Plated.



## Features

- Vinyl Locking Fork Tongue Terminals banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

## Application

Terminal - Fork

## General

Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Small Terminals
UPC	781810029350
UPC 12 Digit	7818100293500

## Dimensions

Dimension - Bolt Size fraction	#8
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - Length Overall inch	0.91 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#8
Dimension - Thread Size	-
Dimension - Z (inch)	0.26 in

## Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	2000
-----------------------	------

## Product Assets

- [3D Models - BA14EL8M\\_MODEL-STEP](#)
- [3D Models - BA14EL8M\\_MODEL-PDF](#)
- [3D Models - BA14EL8M\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50105271](#)



A proud member of the Hubbell Family.

