



# BD24NB Flexible Copper Braid 24 in Long

By Burndy  
Catalog # [BD24NB](#)

Flexible Copper Braid 24 in Long.



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

Catalog Number	BD24NB
Connector Type	Rope lay
Material	Copper
UPC	781810675076
UPC 12 Digit	7818106750766

## Dimensions

Dimension - L Length Overall	610 mm
------------------------------	--------

Dimension - Length Overall	24.00 in
inch	
Length	24 in

## Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

## Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	1500

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50047825](#)
- [Specifications - BD24NB](#)