

## BA16EF2, Vinyl Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # [BA16EF2](#)



Vinyl Fork Terminal For 22 - 16 AWG.

### Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

### Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

### General

Catalog Number	BA16EF2
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	BA-EF
UPC	781810026731
UPC 12 Digit	7818100267311

### Dimensions

Dimension - Bolt Size fraction	#2
Dimension - Hole Size fraction	1/11

Dimension - Hole Size inch	0.09 in
Dimension - Length Overall inch	0.75 in
Dimension - Pad Width inch	0.17 in
Dimension - Stud Size inch	#2
Dimension - Z (inch)	0.23 in

### Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG - 22 AWG; 16 AWG - 18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

### Product Assets

[3D Models - BA16EF2\\_MODEL-PDF](#)  
[3D Models - BA16EF2\\_MODEL-STEP](#)  
[3D Models - BA16EF2\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_BA14EF10\\_LineArt](#)



A Hubbell brand