



# BA16EL10, Vinyl Locking Fork Terminal For 22 - 16 AWG

By Burndy  
Catalog # BA16EL10



Vinyl Locking Fork Terminal For 22 - 16 AWG.

## Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

## Application

For Fast Installation And Security

## General

Connector Type	Locking Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	BA-EL, Locking
UPC	781810026960
UPC 12 Digit	7818100269600

## Dimensions

Dimension - Bolt Size fraction	#10
Dimension - Hole Size fraction	15/79
Dimension - Hole Size inch	0.19 in
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.36 in
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.31 in

## Conductor Related

Conductor - Copper Solid Size Range	20 AWG -22 AWG; 16 AWG -18 AWG
Conductor - Copper Str Size Range	20 AWG - 22 AWG; 16 AWG - 18 AWG
Conductor Size	22 - 16 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_BA14EL10\\_LineArt](#)
- [Sales Drawings - 50094176](#)





A proud member of the Hubbell Family.