



BCSC110800, Black Cold Shrink Sleeve, 8" Length, Jacket OD Range: .39"-.80"

By Burndy
Catalog # [BCSC110800](#)



Black Cold Shrink, Specially formulated silicone rubber offering excellent insulation and moisture resistant sealing for in-line cable connector systems. The rubber sleeves are factory expanded over a removeable, plastic ripcord housing. Installs quickly and easily with no heat gun or other installation tools. Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil. Operating temperature range: -40°C to +105°C.

Features

- Length of tube is consistent before and after application
- Easy, safe installation
- Suitable for wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture resistant seal
- Indoor and outdoor applications
- Rip and Grip Installation does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- cUL insulating cover for wire connectors tested in accordance to UL 486A/B
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable

Application

Cold Shrink, Rated to 2000 Volts, offer insulation and moisture resistant sealing for in-line cable connector systems

General

Catalog Number	BCSC110800
Color	Black
Material	Silicone Rubber
UPC	621945667419

Dimensions

Length	8 in
--------	------

Electrical Ratings

Voltage Rating	2000 V
----------------	--------

Logistics

Carton Quantity	212
-----------------	-----

Product Assets

[Catalog Page - BURNDY Page D2 & D3 - Cold Shrink Catalogs](#) - [BURNDY Master Catalog - Full Line BURNDY Catalog](#) - [BURNDY Master Catalog - Section D - Shrink Tubing](#) - [Interactive Catalog - BURNDY Full-Line Digital Catalog](#) - [Sell Sheets - Clear & Black Cold Shrink - Rated for 2000 Volts](#) - [Specifications - BCSC110800](#)