



BDALHC112350, Power Distribution Block Adder

By Burndy

Catalog # [BDALHC112350](#)



Highly Conductive Al Distribution Block, 310 Amp/Pole, #6 AWG-350 kcmil(Run), #14-#4 AWG(Tap).

General

Catalog Number	BDALHC112350
Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810645482
UPC 12 Digit	7818106454822

Dimensions

Dimension - Height inch	3.55 in
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in
Dimension - Width inch	2.58 in
Dimension - Width mm	66 mm

Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336;4350
Conductor - AL Str Run Range	6-350
Conductor - AL Str Tap	12;10;8;6;5;4

Conductor - AL Str Tap Range	12-4
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300
Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4
Conductor - Copper Str Tap Range	14-4

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	18
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VERSIPOLE_Large_Lineart](#)
- [Sales Drawings - 50038771](#)
- [Specifications - BDALHC112350](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BDALHC112350-SPEC-EN | REV 10/2024