



## BDALHC22350, Power Distribution Block Adder

By Burndy  
Catalog # [BDALHC22350](#)

Highly Conductive Al Distribution Block, 620 Amp/Pole, #6 AWG-350 kcmil(Run & Tap).



### General

Catalog Number	BDALHC22350
Installation Torque Recommended in-lb	275 in-lb
Insulation	Y
Material	Aluminum
Number Of Poles	Adder
Plated	N
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810645581
UPC 12 Digit	7818106455811

### Dimensions

Dimension - Height inch	3.55 in
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in
Dimension - Width inch	2.58 in
Dimension - Width mm	66 mm

### Electrical Ratings

Amperage Rating	620 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336.4;350
------------------------	---

Conductor - AL Str Run Range	6-350
Conductor - AL Str Tap	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;3
Conductor - AL Str Tap Range	6-350
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;3
Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;3
Conductor - Copper Str Tap Range	6-350

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	18
Minimum Pack Quantity	1

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_VERSIPOLE\\_Large\\_Lineart](#)
- [Sales Drawings - 50020385](#)
- [Specifications - BDALHC22350](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BDALHC22350-SPEC-EN | REV 10/2024