


# BDBLCS13LV3DW, Large Flex Rated Lay-in Style Power Distribution Block



By Burndy  
Catalog # [BDBLCS13LV3DW](#)

BURNDY® VERSIPOLE™ Aluminum Lay-in Distribution blocks. 600 Volt Rated; Listed to UL1953. Allows for continuous Run Conductors. Acceptable for Panel mounting or DIN Rail mounting for medium and large sizes. Rated for use with code and flex conductor without requiring ferrules. AL9CU dual rated for use with copper and aluminum conductors. Supplied with Black Cover.

## Features

- Accommodates both Flex and code conductors
- cULus listed to UL1953
- AL9CU Listed for Aluminum or Copper Conductor
- 100kA SCCR rating with correct fusing
- Double-Wide Series include Covers

## General

|                              |                          |
|------------------------------|--------------------------|
| Catalog Number               | BDBLCS13LV3DW            |
| Connector Type               | Power Distribution Block |
| Item Type                    | M                        |
| Material                     | Aluminum                 |
| Material - Base              | NYLON 6/6                |
| Material - Mounting Hardware | Stainless steel          |
| Material Type - Screw        | Tin plated Aluminum      |
| Number Of Poles              | 3                        |
| UPC                          | 621945553682             |
| UPC 12 Digit                 | 621945553682             |

## Dimensions

|        |          |
|--------|----------|
| Height | 4.1 in   |
| Length | 17.84 in |

## Electrical Ratings

|                 |     |
|-----------------|-----|
| Amperage Rating | 545 |
|-----------------|-----|

|                |       |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

## Conductor Related

|                                     |   |
|-------------------------------------|---|
| Conductor - Copper DLO Size Range   | Run - 1111 Kcmil, Tap - # 4 Awg - 500 Kcmil |
| Conductor - Copper Flex H Run Range | 750 - 1000 Flex                             |
| Conductor - Copper Flex H Tap Range | # 4 Awg - 500 Kcmil Flex                    |
| Conductor - Copper Flex I Run Range | 750 - 1000 Flex                             |
| Conductor - Copper Flex I Tap Range | # 4 Awg - 500 Kcmil Flex                    |
| Conductor - Copper Flex K Run Range | 750 - 1000 Flex                             |
| Conductor - Copper Flex K Tap Range | # 4 Awg - 500 Kcmil Flex                    |
| Conductor - Copper Str Run          | 750 - 1000 Kcmil                            |
| Conductor - Copper Str Tap          | # 4 Awg - 500 Kcmil                         |

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50101541](#)
- [Specifications - BDBLCS13LV3DW](#)