



# BDBLCS4K2FS, 2-Pole Flex Rated Finger-Safe Power Distribution Block

By Burndy  
Catalog # [BDBLCS4K2FS](#)



POWER DISTRIBUTION BLOCKS.

## Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of V0

## General

Connector Type	Power Distribution Block
Insulation	Y
Material	Aluminum
Number Of Poles	2
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810676554
UPC 12 Digit	7818106765544

## Dimensions

Dimension - Height inch	4.15
Dimension - L Length Overall mm	157
Dimension - Length Overall inch	6.17

## Electrical Ratings

Amperage Rating	620 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Run Range	6 AWG - 350 kcmil
Conductor - AL Str Tap Range	14 AWG - 2/0 AWG
Conductor - Copper Str Run Range	6 AWG - 350 kcmil
Conductor - Copper Str Tap Range	14 AWG - 2/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	3
Minimum Pack Quantity	1
Pallet Quantity	216

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50059695](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BDBLCS4K2FS-SPEC-EN | REV 5/2024

