



## BDBLCS5SA2, Flex Rated Stud Style Power Distribution Block

By Burndy  
Catalog # BDBLCS5SA2

Image represents single pole



### Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of V0

### General

Catalog Number	BDBLCS5SA2
Connector Type	Power Distribution Block
Material	Aluminum
Trade Name	VERSIPOLE™

UPC 621945518926

### Dimensions

Weight 2.3 lb

### Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BDBLCS5SA2](#)