


BDBLCS10LA3DW, Large Flex Rated Lay-in Style Power Distribution Block

By Burndy
Catalog # [BDBLCS10LA3DW](#)



BURNDY® VERSIPOLE™ Aluminum Lay-in Distribution blocks. 600 Volt Rated; Listed to UL1953. Allows for continuous Run Conductors. Acceptable for Panel mounting or DIN Rail mounting for medium and large sizes. Rated for use with code and flex conductor without requiring ferrules. AL9CU dual rated for use with copper and aluminum conductors. Supplied with Black Cover.

Features

- Accommodates both Flex and code conductors
- cULus listed to UL1953
- AL9CU Listed for Aluminum or Copper Conductor
- 100kA SCCR rating with correct fusing
- Double-Wide Series include Covers

General

Catalog Number	BDBLCS10LA3DW
Connector Type	Power Distribution Block
Item Type	M
Material	Aluminum
Material - Base	NYLON 6/6
Material - Mounting Hardware	Stainless steel
Material Type - Screw	Tin plated Aluminum
Number Of Poles	3
UPC	621945553668
UPC 12 Digit	621945553668

Dimensions

Height	4.1 in
Length	17.84 in

Electrical Ratings

Amperage Rating	475
Voltage Rating	600 V

Conductor Related

Conductor - Copper DLO Size Range	Run - 777 Kcmil, Tap - #14 Awg - # 4 Awg
Conductor - Copper Flex H Run Range	500-750 Flex
Conductor - Copper Flex H Tap Range	# 14 Awg - 4 Awg Flex
Conductor - Copper Flex I Run Range	500-750 Flex
Conductor - Copper Flex I Tap Range	# 14 Awg - 4 Awg Flex
Conductor - Copper Flex K Run Range	500-750 Flex
Conductor - Copper Flex K Tap Range	# 14 Awg - 4 Awg Flex
Conductor - Copper Str Run	500-750 Kcmil
Conductor - Copper Str Tap	# 14 Awg - 4 Awg

Logistics

Carton Quantity	1
Pallet Quantity	84

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50101541](#)
[Specifications - BDBLCS10LA3DW](#)