




# BDBLCS3A1FSKIT, Power Distribution Block Finger Safe Kit

By Burndy  
Catalog # [BDBLCS3A1FSKIT](#)



BURNDY® VERSIPOLE™ Power Distribution Block Finger Safe Kit.

## Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

## General

Connector Type	Power Distribution Block
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	621945450240
UPC 12 Digit	6219454502400

## Electrical Ratings

Rating - Minimum Voltage 600

## Certifications And Compliance

Certification - CSA Approved No  
Certification - cULus Yes  
Standards - RoHS Compliance CM Status

## Logistics

Carton Quantity 20  
Minimum Pack Quantity 1  
Pallet Quantity 1800

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50065165](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BDBLCS3A1FSKIT-SPEC-EN | REV 5/2024