

## BDBLCS5W3, 3-Pole Flex Rated Power Distribution Block

By Burndy  
Catalog # BDBLCS5W3

Distribution block, Three pole Open Style 4 AWG-500 Kcmil (Run),4 AWG-500 Kcmil (Tap).



### Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

### General

Catalog Number	BDBLCS5W3
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676301
UPC 12 Digit	7818106763011

### Dimensions

Dimension - Height inch	4.15
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	231
Dimension - Length Overall inch	9.09

### Electrical Ratings

Amperage Rating	380 A
Rating - Minimum Voltage	600

Voltage - Maximum 600 V

### Conductor Related

Conductor - AL Str Run Range	4 AWG - 500 kcmil
Conductor - AL Str Tap Range	4 AWG - 500 kcmil
Conductor - Copper Str Run Range	4 AWG - 500 kcmil
Conductor - Copper Str Tap Range	4 AWG - 500 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	2
Minimum Pack Quantity	1
Pallet Quantity	144

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50059695](#)  
[Specifications - BDBLCS5W3](#)