

BDBMCS2F1FSKIT, Power Distribution Block Finger Safe Kit

By Burndy
Catalog # BDBMCS2F1FSKIT



Finger safe cover kits.

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Application

For Use On: Suitable for use with aluminum or copper conductors

General

Catalog Number	BDBMCS2F1FSKIT
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	VERSIPOLE

Temperature Rating	194
Trade Name	VERSIPOLE™
Type	Terminal Block Covers
UPC	621945457164
UPC 12 Digit	6219454571644

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Certifications And Compliance

Buy American Compliant	Under Review
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	4800

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50065165](#)
- [Specifications - BDBMCS2F1FSKIT](#)