

BDBLCS6AA, Flex Rated Power Distribution Block Adder

By Burndy
Catalog # BDBLCS6AA

Distribution block, 4-500 Kcmil(Run), 14-4 AWG (Tap).



Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

General

Catalog Number	BDBLCS6AA
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194° F
Trade Name	VERSIPOLE™
Type	BDC
UPC	621945448988
UPC 12 Digit	6219454489888

Dimensions

Dimension - Height inch	4.12
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	141
Dimension - Length Overall inch	5.54
Dimension - Width mm	77 mm

Electrical Ratings

Amperage Rating	760 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Run Range	4 AWG - 500 kcmil
Conductor - AL Str Tap Range	14 AWG - 4 AWG
Conductor - Copper Str Run Range	4 AWG - 500 kcmil
Conductor - Copper Str Tap Range	14 AWG - 4 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	720

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - 50130772 - Adder Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50063029](#)
- [Specifications - BDBLCS6AA](#)