



# BDBMCS3S3S1, Flex Rated Stud Style Power Distribution Block

By Burndy  
Catalog # BDBMCS3S3S1

Power Distribution Block, Medium size, 1-Pole, Stud-to-Stud Style, 3/8" stud Run Side, 3/8" stud Tap Side, 350 Amp Rating.



## Features

- 600 Volt Rated
- Listed to UL1953
- Rated for use with code and flex conductor without requiring ferrules
- AL9CU dual rated for use with copper and aluminum conductors
- Range taking conductor ports can accommodate wire sizes up to 535 DLO and can support up to 5 run conductors and up to 24 tap conductors
- High Short-Circuit Current Rating up to 100kA with proper fusing

## Application

The VERSIPOLE Configurable Series Power Distribution Blocks are used for splicing and distributing power from primary run(s) to secondary/branch circuits

## General

Catalog Number	BDBMCS3S3S1
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Material	Aluminum
Sub Brand	VERSIPOLE
Type	Configurable Power Distribution Blocks
UPC	621945481671

## Dimensions

Height	4.52 in
Length	5.71 in

## Electrical Ratings

Voltage Rating	1000 V
----------------	--------

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	1215

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50081547](#)
- [Specifications - BDBMCS3S3S1](#)