



# BDBMCS5F2FS, 2-Pole Flex Rated Finger-Safe Power Distribution Block

By Burndy  
Catalog # [BDBMCS5F2FS](#)



POWER DISTRIBUTION BLOCKS.

## Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

## General

Connector Type	Power Distribution Block
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	781810676790
UPC 12 Digit	7818106767900

## Dimensions

Height	4.52 in
Length	5.71 in

## Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

## Conductor Related

Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>
----------------	---

## Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50081547](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BDBMCS5F2FS-SPEC-EN | REV 5/2024